

On-line Table: Scanning parameters for each patient

Patient No.	Sequence	2D vs 3D	FOV			Slice		TR (ms)	Flip Angle	No. of Volumes	TE (ms)	TI (ms)	Manufacturer	Model	Field Strength
			(mm)	Rows	Columns	Thickness (mm)	(mm)								
1	BOLD	2D	210	64	64	5	2000	90°	180	30	0	GE	Signa HDxt	3T	
2	BOLD	2D	224	64	64	4	2000	84°	0	34	0	GE	Signa Excite	1.5T	
3	BOLD	2D	240	80	80	6	1000	72°	200	20	0	Philips	Achieva	3T	
4	BOLD	2D	210	64	64	5	2000	90°	180	30	0	Philips	Achieva	3T	
5	BOLD	2D	230	128	128	4	3000	90°	80	35	0	GE	Signa HDxt	3T	
6	BOLD	2D	230	64	64	5	2000	90°	180	30	0	GE	Signa HDxt	3T	
7	BOLD	2D	224	64	64	4	2000	84°	0	34	0	GE	Signa Excite	1.5T	
8	BOLD	2D	212	128	128	4	3000	90°	80	35	0	GE	Signa HDxt	3T	
9	BOLD	2D	240	64	64	3	3000	90°	80	35	0	GE	Signa HDxt	3T	
10	BOLD	2D	240	80	80	6	1000	72°	302	20	0	Philips	Achieva	3T	
11	BOLD	2D	232	128	128	4	3000	90°	80	35	0	GE	Signa HDxt	3T	
12	BOLD	2D	192	64	64	3	2000	77°	165	28	0	Philips	Intera	1.5T	
13	BOLD	2D	220	64	64	3	2400	75°	150	30	0	GE	Signa HDxt	3T	
14	BOLD	2D	192	64	64	3	2000	77°	165	28	0	Philips	Intera	1.5T	
15	BOLD	2D	192	64	64	3	2000	77°	165	28	0	Philips	Intera	1.5T	
16	BOLD	2D	192	64	64	3	2000	77°	165	28	0	Philips	Intera	1.5T	
17	BOLD	2D	224	64	64	4	2000	84°	0	34	0	GE	Signa Excite	1.5T	
1	FLAIR	2D	220	512	512	5	9502	90°	0	125	2250	GE	Signa HDxt	3T	
2	FLAIR	2D	220	256	256	5	8802	90°	0	123	2200	GE	Signa Excite	1.5T	
3	FLAIR	2D	220	560	560	5	11,000	90°	1	125	2800	Philips	Achieva	3T	
4	FLAIR	3D	256	256	256	2	8000	90°	1	337	2400	Philips	Achieva	3T	
5	FLAIR	2D	220	512	512	5	9502	90°	0	125	2250	GE	Signa HDxt	3T	
6	FLAIR	2D	240	512	512	5	9502	90°	0	127	2250	GE	Signa HDxt	3T	
7	FLAIR	2D	220	256	256	5	8802	90°	0	122	2200	GE	Signa Excite	1.5T	
8	FLAIR	2D	220	560	560	5	11,000	90°	1	125	2800	Philips	Achieva	3T	
9	FLAIR	2D	220	512	512	5	9000	90°	0	135	2250	GE	Signa HDxt	3T	
10	FLAIR	2D	220	560	560	5	11,000	90°	1	125	2800	Philips	Achieva	3T	
11	FLAIR	2D	220	512	512	5	9500	90°	0	125	2250	GE	Signa HDxt	3T	
12	FLAIR	3D	250	432	432	1	8000	90°	1	282	2400	Philips	Intera	1.5T	
13	FLAIR	2D	220	512	512	5	9502	90°	0	124	2250	GE	Signa HDxt	3T	
14	FLAIR	3D	250	432	432	1	8000	90°	1	282	2400	Philips	Intera	1.5T	
15	FLAIR	3D	250	432	432	1	8000	90°	1	282	2400	Philips	Intera	1.5T	
16	FLAIR	3D	250	432	432	2	8000	90°	1	299	2400	Philips	Intera	1.5T	
17	FLAIR	2D	240	256	256	5	8802	90°	0	104	2200	GE	Signa Excite	1.5T	
1	TI+Gd	3D	260	512	512	1	10	13°	0	4	450	GE	Signa HDxt	3T	
2	TI+Gd	3D	256	256	256	1	19	20°	0	5	0	GE	Signa Excite	1.5T	
3	TI+Gd	3D	256	256	256	1	18	30°	1	2	0	Philips	Achieva	3T	
4	TI+Gd	3D	256	256	256	1	18	30°	1	2	0	Philips	Achieva	3T	
5	TI+Gd	2D	220	512	512	5	2972	90°	0	16	1238	GE	Signa HDxt	3T	
6	TI+Gd	2D	240	512	512	5	2971	90°	0	16	1238	GE	Signa HDxt	3T	
7	TI+Gd	3D	256	256	256	1	19	20°	0	5	0	GE	Signa Excite	1.5T	
8	TI+Gd	2D	220	512	512	5	3021	90°	0	16	875	GE	Signa HDxt	3T	
9	TI+Gd	2D	260	512	512	5	1983	90°	0	24	851	GE	Signa HDxt	3T	
10	TI+Gd	3D	256	256	256	1	7	8°	1	3	0	Philips	Achieva	3T	
11	TI+Gd	2D	220	512	512	5	3088	90°	0	16	884	GE	Signa HDxt	3T	
12	TI+Gd	3D	256	256	256	1	25	30°	1	6	0	Philips	Intera	1.5T	
13	TI+Gd	3D	260	512	512	1	10	13°	0	4	450	GE	Signa HDxt	3T	
14	TI+Gd	3D	256	256	256	1	25	30°	1	6	0	Philips	Intera	1.5T	
15	TI+Gd	3D	256	256	256	1	25	30°	1	6	0	Philips	Intera	1.5T	
16	TI+Gd	2D	220	256	256	5	450	90°	1	15	0	Philips	Intera	1.5T	
17	TI+Gd	3D	256	256	256	1	19	20°	0	5	0	GE	Signa Excite	1.5T	