

Additional file 7: Table S6. Amplicon coverage data for the technical validation of the custom NGS panel.

Sample	Amplicon mean coverage depth		Uniformity of coverage³	
	Run 1	Run 2	Run 1	Run 2
Tru-Q0	6261	4643	98.17	98.63
Tru-Q1	4589	6455	98.17	98.17
Tru-Q7-rep1	6887	6304	98.63	98.63
Tru-Q7-rep2	4646	6717	98.17	98.17
Seraseq-rep1	7944	6256	98.17	98.17
Seraseq-rep2	6543	6321	98.17	98.63

³ The uniformity of coverage is measured as the percentage of targeted base positions in which the read depth is 20% greater than that of the mean region target coverage depth.